LUMINOR Blackcomb Ultraviolet Systems

Blackcomb UV Disinfection Systems deliver safe, chemical-free disinfection through combining proven UV technology with advanced, user-friendly controls.

The powerful UV rays are applied to the water inside an enclosed stainless steel reactor chamber, and destroys the DNA of micro-organisms, preventing them from multiplying.

A recognised, safe and reliable method of disinfection, UV systems are highly effective against bacteria, viruses, mould spores, algae, parasites and cysts.

The advanced 5.0 Series controller is included standard which offers simplified user controls via the colour display and audible alarm for lamp failure.

All systems can be upgraded with a UV-Sensor which monitors the disinfection capability and alarms when disinfection is reduced.

Benefits

- Chemical free disinfection
- Low maintenance simple design
- Advanced 5.0 Series controller
- 9000 Hour Lamp Life
- Systems from 11-150 litres per minute

- **Applications**
- Point-of-Entry Filtration
- Drinking Water
- Food Service
- Point-of-use filtration
- Rainwater Filtration



| | | | Flow rate (lpm) | | | | | | |
|------------------------|--|----------|----------------------|----------------------|----------------------|--|--|--|--|
| Order Code | Description | Lamp (W) | 16mJ/cm ² | 30mJ/cm ² | 40mJ/cm ² | | | | |
| Lite-Commercial Series | | | | | | | | | |
| UV-LB5-034 | Blackcomb UV System with ½" Ports | 15 | 23 | 11 | 9 | | | | |
| UV-LB5-064 | Blackcomb UV System with ¾" Ports | 30 | 41 | 23 | 17 | | | | |
| UV-LB5-104 | Blackcomb UV System with ¾" Ports | 39 | 77 | 41 | 31 | | | | |
| UV-LB5-154 | Blackcomb UV System with 1" Ports | 50 | 110 | 57 | 45 | | | | |
| Commercial Series | | | | | | | | | |
| UV-LBH5-254 | Blackcomb HO UV System with 1" Ports | 67 | 180 | 95 | 72 | | | | |
| UVS-40-L | Blackcomb HO UV System with 1 1/2" Ports | 101 | 290 | 150 | 120 | | | | |

| System | Chamber Material | Lamp Code | Quartz Code | Reactor Dimensions | Operating presure | Operating Temp | |
|--------------|---------------------|--------------|----------------|-----------------------|-------------------|----------------|--|
| UV-LB5-034 | 304 | RL-290 | RQ-290 | Ø 6.4 x 36.3 | | 2-40°C | |
| UV-LB5-064 | 304 | RL-470 | RQ-470 | Ø 6.4 x 54.1 | | | |
| UV-LB5-104 | 304 | RL-820 | RQ-820 | Ø 6.4 x 89.4 | 10 Der (150 DCI) | | |
| UV-LB5-154 | 304 | RL-999 | RQ-999 | Ø 6.4 x 101.6 | 10 Bar (150 PSI) | | |
| UV-LBH5-254 | 316L | RL-600HO | RQ-600 | Ø 8.9 x 68 | | | |
| UVS-LBH5-404 | 316L | RL-950HO | RQ-950 | Ø 8.9 x 103.4 | | | |

Note: Flow rates are based on UVT of 95%. Please contact 1800 446 500 for other dosage applications